

7 XL 18**Combination spanner**

extra long

Code	ETIM
6080330	EC002176
EAN	UNSPSC
4010886608036	27-11-17-13
Country of origin	eCl@ss
Germany	21-04-01-05
Customs tariff number	
82041100	

**Article description**

- Extra long shaft for deep range of use and more torque
- Chrome-vanadium steel 31CrV3, chrome-plated
- Carefully forged and professionally machined
- Overloading indicated by deformation
- Secure grip thanks to hollow shaft - very ergonomic and handy
- Glare-free look due to matt chrome
- Designed for universal use
- Top-grade industrial quality for the hardest of continuous use
- Jaw: ground precisely to exact nominal size for optimum contact areas
- Ring: 15° offset from shaft, with UD profile for gentle transmission of force

Article information

Contents [Qty of pieces]	1	Width of head 2 [mm]	41 mm
Net weight [kg]	0,233 kg	Head height 2 [mm]	8,5 mm
Total length [mm]	295 mm	Head height 1 [mm]	13,2 mm
Total width [mm]	39 mm	Width of head 1 [mm]	27,8 mm
Total height [mm]	20 mm	Mouth position 1	15°
Surface	chrome-plated	Ring profile	UNIT-DRIVE
Material	31CrV3	Weight	0,510 lbs
Standard	similar to DIN 3113 - form A ISO 3318 ISO 7738	Ring angle	15°
Width across flats 1 [mm]	18		