

Product information

74 06 200

High Leverage Diagonal Cutter

DIN ISO 5749 IEC 60900 DIN EN 60900

- For very tough, continuous use
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction-hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



⚡ 1000V 



| General | |
|--|--|
| Article No. | 74 06 200 |
| EAN | 4003773033820 |
| Pliers | chrome-plated |
| Head | chrome-plated |
| Handles | insulated with multi-component grips, VDE-tested |
| Weight | 304 g |
| Dimensions | 200 x 56 x 26 mm |
| Standard | DIN ISO 5749 DIN EN 60900 IEC 60900 |
| REACH compliant | no |
| RohS compliant | no |
| Technical details | |
| Cutting capacities medium hard wire (diameter) | Ø 4.2 mm |
| Cutting capacities hard wire (diameter) | Ø 3.0 mm |
| Cutting capacities piano wire (diameter) | Ø 2.5 mm |
| VDE tested | yes |
| Classification | |
| eCl@ss 5.1.4 | 21040302 |
| ETIM 5.0 | EC000165 |
| ETIM 6.0 | EC000165 |
| proficl@ss 6.0 | AAA949c004 |
| UNSPSC 13.1 | 27112114 |

technical change and errors excepted