

Main

Range of product	Mureva Styl
Range	Mureva Styl
Product or component type	Shutter control
Number of rocker	2
Switch function	Push-button
Colour tint	Grey (RAL 7016)





Complementary

Device presentation	Mechanism
Technology type	Electromechanical
Device mounting	Surface Flush
Actuator	Rocker
[Ue] rated operational voltage	250 V AC
Condition of use	Indoor/outdoor
Rated current	10 A
Material	Brass SEBS ABS (acrylonitrile butadiene-styrene)
Wire stripping length	13 mm
Clamping connection capacity	1.5...2.5 mm ² for rigid cable(s) 1.5...2.5 mm ² for stranded cable(s) 1.5...2.5 mm ² for flexible cable(s)
Fixing mode	By screws
IP degree of protection	IP55
IK degree of protection	IK07
Width	71 mm
Height	71 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
Depth	40 mm

Environment

Quality labels	EAC CE AENOR NF
Flame retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Standards	EN 60669-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration