



Catalog Number: TY600-175X
Product ID: 7TAG054360R0346
UPC Number: 78620951392
EAN Number: 05415022140842
Status: A

Extra Heavy-Duty Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (221 F), Weather and Ultraviolet Resistant for Indoor or Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 631mm (24.84 Inches), Width of 9mm (0.35 Inches), Thickness of 1.8mm (0.07 Inches), Tensile Strength Rating of 778 Newtons (175 Pounds)

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Extra Heavy Duty
Standard	UL E49405
Width	0.35 in ; 9 mm
Length	24.84 in ; 631 mm
Thickness	0.07 in ; 1.8 mm
Bundle Diameter	7.2 in ; 182.88 mm
Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Plastic Pawl
Tensile Strength	175 pounds ; 780 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	9mm
Length belt/tape/tie	631mm
Tie thickness	1.8mm
Max. bundle diameter	187mm
Min. holding force	778N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	50
Inner Dimensions (inches)	29x6x1.75
Outer Quantity	500
Outer Dimensions (inches)	26.5x8x8
Weight Uom	30.2 lbs. per 1000

For further technical assistance, please contact us...



860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com