



Main

Range	Linergy
Product name	HK
Product or component type	Plug outlet
Poles description	3P
[I _{th}] conventional free air thermal current	32 A
I ² t on activation	200000 A ² .s
Number of points	2
Number of cables	3 cable(s) 4 mm ²
Cable length	1 m
Quantity per set	Set of 6

Complementary

[Ui] rated insulation voltage	600 V conforming to CSA 600 V conforming to UL 690 V conforming to IEC 60439-1
Peak current	25 kA
Width	36 mm
Height	46 mm
Depth	38 mm






Environment

Standards	IEC 60439
Product certifications	UL DNV LROS (Lloyds register of shipping) CSA

Packing Units

Package 1 Weight	148 g
Package 2 Weight	1.01 kg
Package 3 Weight	9.8 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------
