Tower Lights

Direct mount			
LU5	Continuous Light		
I 115-FR	Continuous and Flashing Light		

Direct Mount

with Audible Alarms

K

K

nt

LU5 Series - Medium size **Modular System Indicating Light**

IP-65

85 dB/m

Electronic Alarms:

Open-Collector

Modular

Perfect for OEMs that offer different multi-stack versions in their machine design.

LED Type Light **CE** cUL us

ø50mm (2 in) Round


DC 24V


ø50mm (2 in)

- Colors available: red, yellow, green, blue and clear.
- No tools required to assemble.
- Easy wiring with spring loaded terminal block.
- NPN or PNP open collector compatible.
- **FB** type: Two selectable single-tone alarms, one intermittent and one continuous, with adjustable volume to 85dB (at 1m), and light has 60 flashes per minute.
- Long lasting, bright LEDs.
- Once mounted on a machine, the tower can be easily removed from the terminal base for shipping, and re-installed without tools.



How to Order (Example)





NOTE: See page 57 for wiring diagrams






Assembly Required




BULB		
BULB	No.	
28V 11W	39	
140V 13W	49	
28V 11W	39	
140V 13W	49	
28V 11W	39	
140V 13W	49	
28V 11W	39	
140V 13W	49	



/ Posi	tion	Alarm					
Green	Blue	Clear	Латт				
0.46A	0.46A	0.46A	0.02A				
11W	11W	11W	0.5W				
0.1A	0.1A	0.1A	0.025A				
10W	10W	10W	2.0W				
0.04A	0.04A	0.04A	0.025A				
9W	9W	9W	4.0W				

Bracket Mounting Hole \$\$\phi4\$



Lead Wire Length: Approx 1,000mm from Entry Hole