




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
DF	DO	S		REV PER ECO-08-030008	21JAN2009	PK RL

1. THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308.
2. MAX WIRE INSUL TO BE USED WITH THIS RCPT. IS Ø.054.
3. METAL RETENTION CLIPS ARE INCLUDED IN INSERTS.
- △4 PACKAGE STAMPED M 24308/2-287F.
5. THIS RCPT. WILL ACCEPT SIZE 22 SOCKET CONTACT M 39029/57-354 OR ANY TYCO HDD-22 SOCKET CONTACT.
- △6 MFG'S PART NO. STAMPED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS.
- △7 UL/CSA DESIGNATION STAMPED ON SHELL.
- △8 204514 INK STAMPED, NEAR SIDE.
M24308/2-12F INK STAMPED, FAR SIDE.
- △9 204502-4 INK STAMPED, NEAR SIDE.
- △10 FINISH: BRIGHT TIN PER ASTM-B-545, .000400-.000550 THK OVER COPPER PER AMS2418, .000050 MIN THK.



	△9	△10	STEEL, CLASS G	204502-4
SUPSD BY 204502-1	-	CADMIUM PER QQ-P-416	STEEL, CLASS G	204502-3
SUPSD BY 206501-4	-	CADMIUM PER QQ-P-416	BRASS	204502-2
	△4△6△8	CADMIUM PER QQ-P-416	STEEL, CLASS G	204502-1
REMARKS	FINISH		SHELL MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 01-DEC-87	Tyco Electronics Corporation Harriaburg, PA 17105-3608	
		CHK F.C.BALLEW 25-JAN-88		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD F.C.BALLEW 25-JAN-88	NAME	AMPLIMITE RCPT. FOR SOCKET CONTACTS HI-DENSITY D CONNECTOR SIZE 2 (26 POSN) SERIES 90
	0 PLC ± -	PRODUCT SPEC	SIZE	CAGE CODE
	1 PLC ± -	APPLICATION SPEC	DRAWING NO	RESTRICTED TO
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT -	A100779	204502
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV S