

Product information

18Vx2 Dust Extractor 8L BL LXT



DVC864LZ

Suction Power (DC)	90 W
Continuous Run Time (2 x 5.0Ah)	40 mins
Battery Type	Lithium-ion
Body only machine	1
Voltage	36V (18x2) v
Max Airflow	2.1 m³/min
Max Sealed Suction	9.8 kPa
Tank Capacity	8 litres
Noise sound pressure	70 dB(A)
Noise K factor	2.5 dB(A)
Vibration K factor	1.5 m/sec²
Vibration no load	2.5 m/sec²
Net weight	7.7 - 8.4 kg



STANDARD EQUIPMENT: Nozzle assembly, 2.5m x 38mm hose, 3.5m x 28mm hose, Dust bag, Straight pipe, Bent pipe, Corner nozzle, Front cuffs, Tool box, Stopper

- Auto-Start Wireless System (AWS): Wireless connection to the power-tool via Bluetooth. Enables power take-off of the dust extractor when using a cordless power-tool
- Powered by two 18V Li-ion batteries in series to supply energy to the powerful 36V DC motor drive system.
- Longer run time thanks to brushless motor
- Dry type dust extractor
- Variable suction power by dial
- Large On/Off switch
- HEPA filter with high filtration capacity for clean exhaust air.
- Removable storage box
- Dual battery fuel gauge
- Large bumper protects walls and furniture from bumps and scratches.
- Caster stopper prevents the cleaner from moving unintentionally.
- Compatible with commercial plastic bags

Details correct as of: 6-9-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com