








Socket outlets

Version	DT	Order No.	Price per PU	PU (UNIT, SET, M)	PS*/P. unit	PG
 SCHUKO® socket outlets with hinged lid and increased touch protection and labeling field						
Versions						
• Titanium white (similar to RAL 9010)	A	5UB1 912		1	1/10 units	021
• Electrical white (RAL 1013)	A	5UB1 902		1	1/10 units	021
• Aluminum metallic (similar to RAL 9006)	A	5UB1 932		1	1/10 units	021
• Carbon metallic (similar to RAL 7016)	A	5UB1 922		1	1/10 units	021
• Green (similar to RAL 6018)	A	5UB1 913		1	1/10 units	021
- Without labeling						
- For use with SV ¹⁾						
• Orange (similar to RAL 2004)	A	5UB1 914		1	1/10 units	021
- Without labeling						
- For use with ZSV ²⁾						
Note	Section	Page				
• Degree of protection IP44 for SCHUKO® socket outlets with hinged lid can be achieved using an IP44 seal, for socket outlets, see ...	Accessories and spare parts	1/44	A	5TG4 318	1	1/10 sets 021
• Label sheets, for marking the inserts, see ...	dto.	1/44				
Note						
• Opening angle of the hinged lid, 150°						
• Our free labeling tool can help you create individual labels. Download at: www.siemens.com/labeling-tool						
Footnote						
¹⁾ SV: Safety power supply (AEV).						
²⁾ ZSV: Additional safety power supply (BEV).						
 SCHUKO® socket outlets with hinged lid						
Versions						
• Titanium white (similar to RAL 9010)	A	5UB1 917		1	1/10 units	021
• Electrical white (RAL 1013)	A	5UB1 907		1	1/10 units	021
• Aluminum metallic (similar to RAL 9006)	A	5UB1 937		1	1/10 units	021
• Carbon metallic (similar to RAL 7016)	A	5UB1 927		1	1/10 units	021
Note	Section	Page				
Degree of protection IP44 for SCHUKO® socket outlets with hinged lid can be achieved using an IP44 seal, for socket outlets, see ...	Accessories and spare parts	1/44	A	5TG4 318	1	1/10 sets 021
Note						
Opening angle of the hinged lid, 150°						
 SCHUKO® socket outlets, with hinged lid and increased touch protection						
Versions						
• Titanium white (similar to RAL 9010)	A	5UB1 915		1	1 unit	021
• Electrical white (RAL 1013)	A	5UB1 905		1	1 unit	021
• Aluminum metallic (similar to RAL 9006)	A	5UB1 930		1	1 unit	021
• Carbon metallic (similar to RAL 7016)	A	5UB1 920		1	1 unit	021
• Amber (similar to RAL 1036) 	A	5UB1 920-0		1	1 unit	021
• Piano black (similar to RAL 9005) 	A	5UB1 920-1		1	1 unit	021
• Chilly (similar to RAL 3020) 	A	5UB1 920-2		1	1 unit	021
Note	Section	Page				
Degree of protection IP44 for SCHUKO® socket outlets with hinged lid can be achieved using an IP44 seal, for socket outlets, see ...	Accessories and spare parts	1/44	A	5TG4 318	1	1/10 sets 021
Note						
Opening angle of the hinged lid, 150°						
 Cover plates with hinged lid, increased touch protection and labeling field For converting SCHUKO® socket outlets						
Versions						
• Titanium white (similar to RAL 9010)	A	5UH1 081		1	1/10 units	021
• Electrical white (RAL 1013)	A	5UH1 213		1	1/10 units	021
Note						
<ul style="list-style-type: none"> • Caution: This cover is only suitable as a replacement for SCHUKO® socket outlets with a green touch protection-cover. • Opening angle of the hinged lid, 150° • Our free labeling tool can help you create individual labels. Download at: www.siemens.com/labeling-tool 						

* You can order this quantity or a multiple thereof.