FXT S3S 1M110133 ESD SC FO SR 39

FLEXTRED™ S3S SAFETY BOOTS BLACK 1M110133 ESD SC FO SR

- Flexible and lightweight all-round safety boots for tradesmen protection.
- ENERGY FOAM heel cushioning construction for superior energy return and maximum comfort.
- STEP-RELEASE™ heel for a convenient and rapid shoe removal.
- ROLLCAGE™ heel stabilizer for great stability even in demanding terrain.
- Lace pocket for storing shoelaces to prevent unintentional opening, tripping hazards and lace damage.
- Nubuck water repellent leather upper to protect from water, dust and dirt.
- Scuff cap for increased toe cap protection and durability.
- Metal free construction to conveniently pass through security gates.
- Superior grip to prevent slipping.
- ESD (electrostatic discharge) certified.
- Certified according to EN ISO 20345:2022 S3S ESD SC FO SR.





Description	Shoe size (EU/UK)
Packaging style	Packaging (inner/master)
Article Number	Flextred™ S3S Safety Boots black 1M110133 ESD SC FO SR 36
36/3	Carton box
1/10	
Flextred™ S3S Safety Boots black 1M110133 ESD SC FO SR 37	37/4
Carton box	1/10
	Flextred™ S3S Safety Boots black 1M110133 ESD SC FO SR 38