



2525-520

TOOL TROLLEY with 7 drawers**Body:**

- Dimensions: H 965 x W 720 x D 395 mm
- Working platform in ABS, with 3 compartments for small parts
- Storage compartment with perforated sheet (square perforation 10 x 38 mm) on the handle side
- With handle for easy pushing, pulling and turning
- 1 side wall with square perforation 10 x 38 mm to fix hooks and tools
- All-round heel and impact protection for your safety
- Sheet steel, corrosion resistant and scratch-proof powder-coated, GEDORIT blue

Drawers:

- Central locking with cylinder lock
- 5 wide drawers (W 480 x D 325 x H 75 mm) fully extendable
- 2 large capacity drawers (W 480 x D 325 x H 120 mm) fully extendable, for bulky parts
- Individual drawer locking, single-hand operation
- Ball-bearing guide rails
- Can be individually equipped with length and crosswise dividers (can be ordered individually, not for the large capacity drawers)
- Load capacity per drawer 40 kg
- Sheet steel, corrosion resistant and scratch-proof powder-coated, GEDORIT silver

GEDORE High-performance chassis:

- Total load capacity 330 kg
- 2 high-performance wheels on roller bearings (fixed castors Ø 140 mm)
- 2 smooth running wheels on ball bearings (swivel castors Ø 100 mm), one with total brake
- The GEDORE trapezoidal axle construction secures smooth running, manoeuvrability and track-keeping also in case of maximum loads

Accessories:

- 10-piece hook assortment
- 8 length- (LT) and 2 crosswise (QT) dividers from zinc-plated sheet steel

Options:

- Can be equipped with GEDORE tool modules (1500 ES/1500 CT)
- Optionally extendable with wooden plate No. 2525 HP
- Special colours and designs available on request
- Delivery without tools and accessories

H	W	D	LD	CD		Code	No.
965	720	395	8x	2x	67.0	1587102	2525-520



2535

TOOL TROLLEY DUO with 4 drawers**Body:**

- Overall dimensions: H 965 x W 625 x D 395 mm
- Dimensions upper part: H 350 x W 625 x D 395 mm
- Dimensions lower part: H 635 x W 625 x D 395 mm
- Top and bottom of mobile tool chest joined by quick-action latches for easy separation each with two carry handles
- Each has a working platform in ABS, with 3 compartments for small parts
- Lower part with all-round heel and impact protection for your safety
- Sheet steel, corrosion resistant and scratch-proof powder-coated, GEDORIT blue

Drawers:

- Separate locking for top and bottom of mobile tool chest with two identical cylinder locks
- Upper part with 3 wide drawers (W 480 x D 325 x H 79 mm) fully extendable, removable
- Lower part with 1 wide drawer (W 480 x D 325 x H 79 mm) fully extendable, removable, and a large storage compartment
- Individual drawer locking, single-hand operation
- Ball-bearing guide rails

- Can be individually equipped with length and crosswise dividers (can be ordered individually, not for the deep storage)
- Load capacity per drawer 40 kg

- Sheet steel, corrosion resistant and scratch-proof powder-coated, GEDORIT silver

GEDORE Chassis

- Total load capacity 250 kg
- 2 high-performance wheels on roller bearings (fixed castors Ø 140 mm)
- 2 smooth running wheels on ball bearings (swivel castors Ø 100 mm), one with total brake
- The GEDORE trapezoidal axle construction secures smooth running, manoeuvrability and track-keeping also in case of maximum loads

Accessories:

- Length- (LT) and crosswise (QT) dividers from zinc-plated sheet steel

Options:

- Can be equipped with GEDORE tool modules (1500 ES/1500 CT)
- Special colours and designs available on request
- Delivery without tools and accessories

H	W	D	LD	CD		Code	No.
965	625	395	4x	2x	50.0	1892495	2535
350	625	395	3x	2x	27.0	1906445	2535 SMA

