

Features

- Enhanced, high performance Cat6 cable for LAN applications or future proofing of structured cabling systems
- Conforms to ANSI/TIA-568.2-D & ISO/IEC 11801-1
- HDPE & Foam PE Insulation
- Mylar & AL-Mylar Tape Construction
- Backwards Compatible to CAT 3 CAT 5 CAT 5E
- Operation Temp -20c - 60c
- Conductor DC Resistance $\leq 9.38 \Omega$ /100m

RS PRO Ethernet Cable

RS Stock No.: 0199203



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Innovative design with VLZ tech for superior audio fidelity. The RS Pro Unterminated Cat6 type cables have primary application use for both home and office computer networks. This cable is compliance with CE, UKCA, RoHS, REACH and UL standards.

General Specification

LAN Category	Cat6
Length (mm or m)	305m
Terminated/Unterminated	Unterminated
Shield Type	F/UTP
Shielded/Unshielded	Shielded
Coding	T568B
Sheath Colour	Violet
Outer Sheath Material	LSZH
IP Rating	IP67
Core Strands	8
Fire Behaviour	LSZH
Voltage Rating	300V

Conductor Strand Type	Stranded
American Wire Gauge	23 AWG
Cable Shape	Round
Number of Strands	8
Outer Diameter(mm)	7mm
Cross Sectional Area(mm)	0.1303mm
Current Rating(A)	2.2A
Applications	Cat6 type cables have primary application use for both home and office computer networks