

IN 19 L 14-140

Screwdriver bit socket 1/2"

Code
6158620

ETIM
EC002157

EAN
4010886615867

UNSPSC
27-11-17-01

Country of origin
Germany

eCl@ss
21-04-04-02

Customs tariff number
82079030



Article description

- Acc. to DIN 7422
- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- Chromed
- With pressed-in pin in GEDORE vanadium special steel, manganese-phosphated

Article information

Contents (Qty of pieces)	1	Drive connector square female [inch]	1/2"
Net weight [kg]	0,257 kg	Standard	DIN 7422 DIN 3120 - C 12,5 ISO 1174
Total length [mm]	140 mm	Width across flats l [mm]	14
Total width [mm]	24,7 mm	Backup	Ball Catching Cricket
Surface	chrome-plated	Tip length	100,0 mm
Material	Chrome-vanadium steel	Insert Ø Actuator	24,7 mm
Drive connector square female (metric)	12,5 mm		