



<b>Product-Nr.</b>	130190-11
<b>EAN:</b>	4260556626970
<b>Model:</b>	DOMELED IO-Link
Order number:	130190-11
<b>Model:</b>	DOMELED IO-Link
Illuminant:	LE-d42-io
Power consumption white:	1,8 W
White lamp luminous flux:	282 lm
Lamp luminous efficiency:	160 lm/W
Light colour white:	5000K (daylight white)
Power consumption RED:	1,5 W
Lamp luminous flux RED:	95 lm
Power consumption GREEN:	1,3 W
Lamp luminous flux GREEN:	227 lm
Power consumption YELLOW:	1,3 W
Lamp luminous flux YELLOW:	146 lm
Power consumption BLUE:	1,7 W
Lamp luminous flux BLUE:	66 lm
Light distribution:	direct
Number of poles:	4
Connected load:	24 V DC -5 / +10% [LEDs], 24 V DC +/- 25% [IO-Link communication]
Maximum power consumption White:	90 mA
Maximum current consumption Colors:	90 mA
Power supply:	external
Connection (connector):	M12 A-coded
Degree of protection:	IP67
Class of protection:	III
Beam angle (optics):	180°
Operating temperature:	-20 °C - +50 °C (-4 °F - 122 °F)
Storage temperature:	-20 °C - +80 °C (-4 °F - 176 °F)
Colour rendering WHITE (Ra):	>85
Lamps lifetime:	> 60,000 h (L80/B10)
Housing material:	PC
Height [B] x Width [C]:	74 mm x 50 mm (~2,91" x ~1,97")
Length [A]:	50 mm (~1,97")
Mounting:	optional
Weight (net):	70 g (~2 oz)
Gross weight:	100 g (~4 oz)
Risk group (DIN EN 62471):	free group
Markings:	CE, UKCA, ETL Listed (5003529)
Dimmable:	yes
Feature:	IO-Link