

Data sheet for three-phase Squirrel-Cage-Motors



Ordering data : 1LA7060-4AB10

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Electrical data:

Rated motor voltage :	(1) 230 VD/400 VY, 50 Hz, 460 VY, 60 Hz					
Frequency :	50 Hz		60 Hz			
Rated power :	0.12 kW		0.14 kW			
Rated motor speed :	1350 1/ min		1650 1/ min			
Rated motor torque :	0.8 Nm		0.8 Nm			
Rated motor current (IE) :	VD	VY	VY			
	0.73 A	0.42 A	0.43 A			
Starting / rated motor current :	2.8		3.1			
Breakdown / rated motor	2.0		2.1			
Starting / rated motor torque :	1.9		2.0			
	4/4	3/4	2/4	4/4	3/4	2/4
Efficiency %	53.6%	52.1%	47.6%	56.0%	54.5%	50.0%
Power factor :	0.75	0.69	0.56	0.74	0.68	0.55
Efficiency class :	-/-		-/-			

Mechanical data:

Sound pressure level 50 Hz/60Hz (load) :	42 dB(A)	46 dB(A)
Moment of inertia :	0.00029 kg*m ²	
Bearing DE :	6201 2ZC3	
Bearing NDE :	6201 2ZC3	
Type of bearing :	Floating bearings pre-loaded DE (standard)	
Condensate drainage holes :	No	
Regreasing device :	No	
Lubricants :	Esso Unirex N3	
Grease lifetime/Relubrication interval :	40000 h	
Quantity of grease for relubrication :	null g	
External earthing terminal :	No	
Coating :	Special paint finish RAL 7030 stone gray	

Explosion protection:

Type of protection : without (standard)

Environmental conditions:

Ambient temperature :	-20 °C - +40 °C
Altitude above sea level :	1000 m
Standards and specifications :	IEC, DIN, ISO, VDE, EN

General data:

Frame size	063 M
Type of construction :	(0) IM B3 / B6 / B7 / B8 / V5 without canopy
Weight in kg, without optional accessories :	3.50 kg
Frame material :	Aluminum
Degree of protection :	IP 55
Method of cooling, TEFC :	IC 411
Vibration class :	A (Standard)
Insulation :	155(F) to 130(B)
Duty type :	S1 - continuous duty
Direction of rotation :	Bi-directional

Terminal box:

Material of terminal box :	Aluminum
Type of terminal box :	gk 030
Contact screw thread :	M4
Max. cross-sectional area :	1.50 mm ²
Cable diameter from ... to ... :	9.00 mm - 17.00 mm
Cable entry :	1xM25x1,5-1xM16x1,5
Cable gland :	2 plugs

Special design: