

## HAR44EL



FALL ARRESTER HARNESS WITH BELT - 4 ANCHORAGE POINTS - DIELECTRIC

Ref. HAR44EL\_



### Product specifications

Dielectric harness with positioning belt. 2 fall arrester anchorage points (back - front). 4 adjustable buckles. Positioning belt with thermoformed back closed with wide Velcro for more comfort. 180° rotation. 2 lateral anchorage points for work positioning. Sponge back lining. Buckles with plastic coating. Material insulates to 20kV.

Straps: Polyester.

Buckles: 100% plastic coating.

#### COLOUR

Black-Grey

#### SIZE

S/M/L, XL/XXL

## Product Use - Risks



Fall



Construction / Civil engineering



Heavy industry



Services / Logistics



Oil / Gas



Wind energy



Vertical movement on a permanent structure



Long vertical movement or movement on

inclined surface



Short vertical movement or movement on inclined surface (less than 3 m)



Vertical movement, confined space



Long movement with multi connection /disconnection



Work positioning



Restraint



Long horizontal movement on horizontal surface



Long horizontal movement on vertical structure



Short horizontal movement (less than 3 m)

## Product's highlights & user's benefits

DIELECTRIC



2 accessory attachment holders incorporated into the belt



Rotation 180°

## Certifications and Standards



PPE DIRECTIVE 89/686/EEC

EN363 : 2008 Personal fall protection equipment - Personal fall protection systems

EN364 : 1992 Personal fall protection equipment : Test method

EN365 : 2004 General requirements for the instructions for use and the marking

EN361 : 2002 Personal protection equipment against falls from a height - Full body harnesses

EN358 : 1999 Personal fall protection equipment for work positioning and prevention of falls from a height - Belts for work positioning and restraint and work positioning lanyards.

## References

References	Bar code	COLOUR	SIZE		
HAR44ELGT	3295249203504	Black-Grey	S/M/L	5	-
HAR44ELXX	3295249204723	Black-Grey	XL/XXL	5	-