

Features

- **Exceptional Durability:** Crafted from premium NR/SBR rubber for long-lasting resilience
- **Versatile Installation:** No pre-drilled holes for flexible mounting; optional pre-drilling available upon request.
- **Wide Applications:** Ideal for marine docks, parking spaces, factories, warehouses, and industrial environments.

RS PRO Standard Rubber D-Fender 2.44m Length x 75mm Width x 66mm Height SBR/NR

Vendor Partcode.: 0688165



RS PRO is our own brand range and brings you a wide range of high-quality, great value products offering you more choice. Trusted by engineers all over the world, every part of every RS PRO product has been rigorously tested against demanding industry standards; they're only given the RS PRO Seal of Approval if we're confident of their exceptional quality, which means you can be confident too.

Product Description IBUTE

RS PRO NR/SBR D-Fenders are high-quality rubber bumpers designed to safeguard boats, docks, warehouses, and loading bays from accidental impacts. Made from durable NR/SBR rubber, they provide excellent resilience against harsh environmental conditions, making them suitable for both indoor and outdoor applications. Their versatile installation allows them to be mounted on floors or walls, ensuring optimal protection across various industries. Whether used in marine settings, parking areas, or factory production lines, RS PRO D-Fenders help minimize damage while enhancing overall safety.

Specifications

Material	SBR/NR
Colour	Black
Length	2440mm
Width	75mm
Height	66mm
Wall Thickness	15mm
Diameter	8mm
Hardness	80ShA
Density (g/cm³)	1.9
Weight (Kg)	14.5

Approvals

Standards Met	REACH
----------------------	-------