



ENGLISH

Datasheet

RS Pro Portable Speaker

RS Stock No: **535-0221**



Product Details

RS Pro portable speaker is IP53 rated and is designed for speech and music reproduction, providing quality sound for all requirements. It has an ABS construction for durability. The speaker frequency response ranges from 100 Hz - 20 kHz.

Features and Benefits

- 20 W rms
- 110° dispersion output
- 20 W, 15 W, 10 W, 5 W, 2.5 W and 8 Ω power taps
- Operates temperature range: -20 to +50°C
- ABS construction

**Specifications:**

Colour	White
Diameter	174 mm
Enclosure Material	ABS
Frequency Response	100 Hz to 20 kHz
Height	269 mm
Impedance	8 Ω
Maximum Frequency Response	20 kHz
Maximum Rated Power	20 W
Minimum Frequency Response	100 Hz
Sound Pressure Level	90 dB
Weight	2.55 kg
IP Rating	IP53
Temperature Rating	-20 to +50°C