

77524

Floor squeegee
w/Replacement Cassette,
400 mm, Red



Ideal for removing water and food debris from all types of flooring, this double-bladed cell rubber squeegee can be used with any Vikan handle. The cassette can be removed easily for cleaning or replacement (Series 77725 or 77729 for replacement blades).

Technical Data

Item Number	77524
Material	Polypropylene Cellular rubber
Complies with (EC) 1935/2004 on food contact materials¹	No
FDA compliant raw material (CFR 21)	No
Is Halal compliant	Yes
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	480 Pcs.
Quantity Per Layer (Pallet)	60 Pcs.
Box Length	415 mm
Box Width	295 mm
Box Height	215 mm
Length/Depth	400 mm
Width	90 mm
Height	110 mm
Gross Weight	0,23 kg
Net Weight	0,2 kg
Cubik metre	0,004 M3
Max. cleaning temperature (Dishwasher)	80 °C
Max usage temperature (non food contact)	80 °C
Min. usage temperature³	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
GTIN-13 Number	5705020775246
GTIN-14 Number (Box quantity)	15705020775243
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

3. Do not store the product below 0° Celsius.