

Section Links

A045 | A040 | A095 | A090 | A195 | A190 | A080 | A085 | A087 | A200 | A070 | A210 | A300 | A315 | **A089** | A125 | A105 | A205

Product Details

A089 Hygienic Stainless Steel Machine Mounts



Part No.	Thread Size D1 (mm)	Thread Length L (mm)	Base Diameter D2 (mm)	Adjustment H3 (mm)	Min Height H1 (mm)	Overall Height H (mm)	Maximum Recommended Load (kg)
A089/001	M12	68	55	25	70	104	750
A089/002	M12	92	55	50	95	154	750
A089/003	M16	68	75	50	75	130	1750
A089/004	M16	92	75	50	100	180	1750
A089/005	M20	68	100	25	85	136	2500
A089/006	M20	92	100	50	110	186	2500

Dimensions are approximate

General

The Nu-Tech Hygienic Machine Mount has been designed for those industries and applications where Hygiene is of the up most importance. The threaded section which is exposed on standard levelling feet and an area of potential contamination has been replaced with a stud manufactured with only a part threaded section which is then covered by an adjustable sleeved collar. The base has been designed with smooth polished easy clean profile and incorporates a rubber seal between the stud and base interface. Ideally suited for applications within the Food, Dairy, Medical, Pharmaceutical industries and Laboratory/Clean Room environments.