

Datasheet

RS Pro Closed End Wire Splice Connector, Clear, Insulated, Tin Plated 0.5 → 1.5 mm²

RS Stock No: **534-907**



Product Details

RS Pro closed end wire splice connector in clear colour, has tin plated copper sleeves and transparent nylon 6.6 insulation for durability. It accommodates wire size of 0.5 to 1.5 mm². This closed end wire splice is ideal for electrically joining cables or for storing/insulating the ends of spare cables, which may be required at a later date.

Features and Benefits

- Tin plated copper sleeves and transparent nylon 6.6 insulation
- Suitable for electrically joining cables or for storing/insulating the ends of spare cables
- Closed end splice type

**Specifications:**

Colour	Clear
Contact Material	Copper
Contact Plating	Tin
Insulation	Insulated
Insulation Material	Nylon
Shrouded	Shrouded
Splice Type	Closed End
Diameter	6.6 mm
Maximum Wire Size (AWG)	16 AWG
Maximum Wire Size (mm ²)	1.5 mm ²
Minimum Wire Size (AWG)	22 AWG
Minimum Wire Size (mm ²)	0.5 mm ²
Overall Length	18.1 mm
Wire Size	0.5 to 1.5 mm ²
Maximum Voltage & Temperature	600V 105