

FEATURES

- Black RJ45 (6 way)
- 2 Ports Socket to Socket
- UTP Unshielded coupler
- PBT Material for Durable design
- Phosphor bronze contacts with gold over nickel plating
- Dimensions: 20.55 x 14.48 x 26.98 mm

RS PRO RJ45 Coupler, 2 Port, UTP

RS Stock No.: 186-3149



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS PRO, this RJ45 Modular Coupler enables RJ45 connector plugs and cable assemblies to be patched together straight through a patch panel or blank faceplates. This unshielded modular inline coupler has a durable design and can easily press-fit into pre-cut panels. This is ideal for those who need a custom network architecture solution.

General Specifications

Type	Coupler
Interface Type	RJ45
Number of Ports	2
Shield Type	UTP
Wiring Configuration	Straight Through
Colour	Black
Contact plating	Gold over Nickel
Housing Material	Glass Filled PET UL 94V-0
Application	RJ45 connectors and cables are typically used for internet connections, forming either local area (LAN) or wide area (WAN) networks. This inline coupler can be used to patch two RJ45 cable assemblies together, and as such is ideal for network patching, or even simply as a cable extension solution. For workspaces where Wi-Fi is restricted, or when a more dependable hardwire connection is required, this adapter allows you more mobility around an ethernet connection. For connecting personal computers to modems and network architecture, this adapter is ideal.

Mechanical Specifications

Length	20.55mm
Width	14.48mm
Depth	26.96mm

Approvals

Compliance/Certifications	UL 94V-0/2011/65/EU and 2015/863
---------------------------	----------------------------------



