

NORTON

SAINT-GOBAIN

Reshaping
your
world.**R222 - Handy Rolls****Handy Rolls Norton-R222-38x25m#180**

Artical Number: 63642531806

EAN: 3157620181743

**Description**

R222 handy rolls are designed for manual applications. The high flexibility of the cloth in combination with the wide grit range, from coarse to fine, provides an excellent tool for a variety of applications including deburring, rust removal and finishing metal.

Features & Benefits

J-weight cloth backing

Premium aluminium oxide abrasive

Dispenser unit

Application Data

Material Application: NON-FERROUS
Machine: Manual application
Process: Sanding

Equipments:

**Technical Data**

| | | | |
|------------------|----------------|---------|-------|
| MarketingCAP: | R222 | Length: | |
| BackingMaterial: | Light Cotton J | Width: | 38 mm |
| Grit: | 180 | | |
| Color: | Maroon | | |
| CoatedShape: | Rolls Trimmed | | |
| CoatedSubShape: | Handyroll | | |
| | | Shape: | |

Logistic Data

| | | | |
|--------------------------|----------|----------------------------|-------------------------|
| Naked Product Weight: | 0.058 kg | Packed Product Dimension: | 180 mm x 480 mm x 46 mm |
| Naked Product Dimension: | 38x25m | pack Qty (parts per pack): | 1 pc |
| Units per part: | 1 pc | Packed Product Weight: | 0.28 kg |