

#### **FEATURES**

- Impedance protected shaded pole motor
- Smooth and efficient air flow
- PBT UL94V-0 thermoplastic impeller
- ideal for industrial applications

# RS PRO, 230 V ac, AC Axial Fan, 172 x 51mm, 235 cfm, 35W

RS Stock No.: 619-6882



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



### **Product Description**

Brought to you by RS PRO, a range of AC dual ball bearing axial fans offering a cost effective cooling solution without sacrificing on quality or reliability. Provided are a robust die-cast aluminium frame and an AC shaded pole impedance protected motor, these fans are ideal for a multitude of applications. All models are highly reliable and excellent quality.

#### **General Specifications**

Air Flow	235CFM
Fan Speed	3200rpm
Noise Level	52dB
Direction of Curve	Forward
Frame	Die Cast Aluminium
Impeller	PBT UL94V-0 Plastic
Alarm Function	No
IP Rating	IP44
Applications	Server racks, Electrical cabinets and enclosures; Production Lines, Ceiling fan/ventilation Desktop computers, Motor engines (radiator in a car), Generators, Air compressors



### **Electrical Specifications**

AC or DC Operation	AC
Power Consumption	35W
Supply Voltage	230VAC
Maximum Current	150mA
Frequency in Hz	50/60
Dielectric Strength	1 minute@1500 VAC, 50/60 Hz

### **Mechanical Specifications**

Dimensions	172mm x 150mm
Height	172mm
Width	150mm
Depth	51mm
Bearing Type	Ball
Life Expectancy	60,000 hours (L10)

# **Operation Environment Specifications**

Operating Temperature	-10°C to 70°C
-----------------------	---------------

## **Approvals**

Compliance/Certifications	UL, cUL, TUV, CE, UL94-V0
---------------------------	---------------------------







## Dimensions: (mm)

