

$$12\text{ V} = 30 = 24\text{ V}$$

### → Model PB 1

- Type Selfpriming, rotary vane pump with Bypass valve and built in strainer
- Protection IP55
- Connections 1" BSP/G
- Cable 4 m with Battery clips and fuse
- Handle yes
- Switch on/off yes

30 12 or 24 V DC 45-60 LPM



### → Model ECOKIT 1

- also available with gun holder and telescopic metal pipe (ECOKIT 2)**
- Type Selfpriming, rotary vane pumps with By-pass valve
  - Protection IP55
  - Connections 3/4" BSP/G
  - Cable 2 m with Battery clips and fuse
  - Handle Yes
  - Switch on/off Yes
  - Meter no
  - Discharge Hose 4 m Ø 19 rubber, 1" x 3/4" BSP/G
  - Suction Hose 2 m Ø 25 PVC + Filter
  - Nozzle Aluminium nozzle 1" BSP/G
  - Wall panel no

30 12 or 24 V DC 40 LPM



### → Model WALL TECH

- also available 45 & 60 lpm with related accessories**
- Type Selfpriming, rotary vane pumps with By-pass valve
  - Protection IP55
  - Connections 3/4" BSP/G (Pump) - 1" BSP/G (Meter)
  - Cable 2 m with Battery clips and fuse
  - Handle Yes
  - Switch on/off Yes
  - Meter TECH FLOW 3C mechanical meter
  - Discharge Hose 4 m Ø 19 rubber, 1" x 1" BSP/G
  - Suction Hose No
  - Nozzle Aluminium nozzle 1" BSP/G
  - Wall panel Yes

30 12 or 24 V DC 40 LPM



### → Model KPT

- Type Selfpriming, rotary vane pumps with By-pass valve
- Protection IP55
- Connections 3/4" BSP/G
- Cable 2 m with Battery clips and fuse
- Handle Yes
- Switch on/off Yes
- Discharge Hose No
- Filter Yes
- Bung thread No
- Nozzle No

30 12 or 24 V DC 40 LPM



### → Model KIT BATTERIA

- Type Selfpriming, rotary vane pumps with By-pass valve
- Protection IP55
- Connections 3/4" BSP/G
- Cable 2 m with Battery clips and fuse
- Handle Yes
- Switch on/off Yes
- Discharge Hose 4 m Ø 19 rubber, 1" x 3/4" BSP/G
- Suction Hose 2 m Ø 25 PVC + Filter
- Bung thread No
- Nozzle Aluminium nozzle 1" BSP/G

30 12 or 24 V DC 40 LPM



$$12\text{ V} = 30 = 24\text{ V}$$