

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability.
- **Flanged Design:** Ensures secure positioning and easy installation.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads effectively.
- **Bore Size of 20.02 mm:** Fits standard shafts for versatile use.
- **Outside Diameter of 24.05 mm:** Compatible with common housing dimensions.

RS PRO 20.02 mm Flanged Plain Bearing

RS Stock No: 529-052



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 20.02 mm Flanged Plain Bearing is designed for applications requiring reliable rotational movement with minimal friction. Made from sintered bronze, this bearing is ideal for use in environments where durability and resistance to wear are crucial.

General Specifications

Bore Size	20.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	24.05 mm
Width	20 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

