





214900

OH33-RMN-PT-G3-T4

Retroreflective diffuse sensors with background suppression

- Compact design
- Long range
- Ideal background suppression
- Push-pull output with npn or npn function
- Switch for light/dark switching
- IO-Link
- Measuring function
- Sensing range and window function can be parameterized in mm



BK: black

BN: brown

BU: blue

WH: white

Function



Technical data (typ.)

+20°C, 24 V DC

Electrical features

Service voltage	10 ... 30 V DC
No-load current (max.)	< 45 mA
Inverse polarity protection	Yes
Short-circuit protection	Yes

Mechanical features

Housing dimensions	31 x 20 x 11 mm
Housing length	20 mm
Housing height	31 mm
Housing width	11 mm
Housing material	Plastic
Material	Plastic (Window / optics)
Weight	20 g

Certifications, approvals

Protection class	III
Approvals	UL



214900

OH33-RMN-PT-G3-T4

Retroreflective diffuse sensors with background suppression

Technical data (typ.)

+20°C, 24 V DC

General features

Operating principle	Diffuse sensor with background suppression
Evaluation	digital
Design	Cuboid design
Werkseinstellung	Switching frequency (500 Hz (STANDARD))

Output, input, interface

Switching output	Push-pull, 100 mA, NO/NC, switchable
Voltage drop (max.)	1 V
Interface	IO-Link (V1.1, COM2 38.4 kBd, Smart Sensor Profile)

Optical data

Light source	LED
Color	Red
Wavelength	620 nm
Background suppression	Yes
Light spot size	Ø 7 mm (at distance of 100 mm)

Detection range, measuring range, tolerance limits

Range	20 ... 200 mm
Standardized measuring plate	200 x 200 mm (white)

Display, operation

Sensitivity adjustment	Potentiometer, IO-Link
Display	LED green - Status, yellow - Switching output 1

Time behavior

Switching frequency	50 Hz ... 500 Hz (50 Hz (PRECISION))
---------------------	--------------------------------------

Ambient conditions

Ambient temperature during operation	-25 ... +60 °C
Protection type	IP 67


Electrical connection

Connection	Connector, M8, 4-pin
------------	----------------------

Accessories

Connection cable	TK ... /4
------------------	-----------

Background suppression






214900

OH33-RMN-PT-G3-T4

Retroreflective diffuse sensors with background suppression

Typical detection diagram (white 90%)



More information / accessories

<https://www.di-soric.com/214900>