

OUTDOOR LIGHTING



NH1061W



NH1069W



HEOD1309W **NEW**

IP44 STAINLESS STEEL WALL LIGHTS

Upright Wall Light

Integral fitted 16 x LED's @ 1.2 watt cool white (non-replaceable). Electrical termination via 10 Amp connector block. Wall mounted.
Overall Ø 60mm x H 160mm, base Ø 85mm, depth from wall 125mm

Code	Description	Box QTY (Inner/Outer)	Price List Page No.
NH1061W	Upright	1/25	48



Angled Wall Light

Integral fitted 16 x LED's @ 1.2 watt cool white (non-replaceable). Electrical termination via 10 Amp connector block. Wall mounted.
Overall Ø 60mm x H 250mm

Code	Description	Box QTY (Inner/Outer)	Price List Page No.
NH1069W	Angled	1/25	48



OUTDOOR HEATERS & TUBES

NEW

1300W Infrared Heater

R7s Lampholder. R7s 1300watt lamp included (replacement lamp - product code HEOT1300W see below). Electrical termination via 3m of HQ5RN-F 3core 1.5mm² cable with a 13amp rubber plug top. Mesh grill front cover. Heating area 8 to 10m² (depending on fixing height, minimum mounting height 1.8m.
W 345mm x D 180mm x H 370mm (including fixing arm)

Code	Description	Box QTY (Inner/Outer)	Price List Page No.
HEOD1309W	White	1/6	48
HEOD1309BK	Black	1/6	48
HEOT1300W	R7s Double Ended Lamp L 254mm	1/10	48

