

HP J9151E Compatible SFP+ Transceiver Module - 10GBase-LR

Product ID: J9151E-ST



The J9151E-ST is a HP J9151E compatible fiber transceiver module that has been designed, programmed and tested to work with HP brand switches and routers. It delivers dependable 10 GbE connectivity over fiber cable, for 10GBase-LR compliant networks, with a maximum distance of up to 10 km (6.2 mi).

Technical Specifications:

- **Wavelength:** 1310nm
- **Maximum Data Transfer Rate:** 10 Gbps
- **Type:** Single Mode Fiber
- **Connection Type:** LC Connector
- **Maximum Transfer Distance:** 10 km (6.2 mi)
- **MTBF:** 1,386,624,697 hours
- **Power Consumption:** < 1.3W
- **Digital Diagnostics Monitoring (DDM):** Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

StarTech.com SFPs

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP+ modules and direct-attach SFP+ cables, providing the convenience and reliability you need to ensure dependable network performance.

**Certifications, Reports
and Compatibility**



Features

- 100% Compatibility with HP J9151E guaranteed
- StarTech.com SFP modules are backed by a lifetime warranty
- Meets or exceeds OEM specifications and Multi-Source Agreement (MSA) industry standards
- Low power consumption of > 1.3W
- Hot-swappable with fiber-optic modules

	Warranty	Lifetime
Hardware	Compatible Brand	HP®
Performance	Maximum Data Transfer Rate	10.00 Gbps
	Power Consumption (In Watts)	< 1.3W
Physical Characteristics	Product Height	13.700
	Product Length	0.5 in [1.4 cm]
	Product Width	58.400
	Weight of Product	21.000
Packaging Information	Package Height	31.000
	Package Length	115.000
	Package Width	90.000
	Shipping (Package) Weight	50.000
What's in the Box	Included in Package	1 - SFP+ Transceiver

Product appearance and specifications are subject to change without notice.