



### Main

Range of product	ConneXium
Product or component type	Ethernet TCP/IP managed switch
Concept	Transparent Ready
Communication port protocol	Ethernet TCP/IP
Port Ethernet	10BASE-T/100BASE-TX - 16 port(s) copper cable
Maximum number of switches in cascade	Unlimited

### Complementary

Integrated connection type	Shielded RJ45 copper cable
Transmission support medium	Twisted shielded pairs cable CAT 5E for copper cable
Ethernet service	Configuration via web server Data stream control FDR IGMP Snooping Multicast filtering Priority port Rapid Spanning Tree Protocol (RSTP) Secure port SMTP V3 SNTP client VLAN
Maximum number of switches in a ring	50
Redundancy	Redundant power supplies Redundant single ring Ring coupling
[Us] rated supply voltage	24 V
Supply voltage limits	18...30 V AC SELV 9.6...60 V DC SELV
Power consumption in W	9.4 W
Electrical connection	Removable connector 6 ways power supply

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting support	35 mm symmetrical DIN rail
Marking	CE
Local signalling	1 LED fault 2 LEDs P1 P2 power supplies 1 LED ring manager 1 LED stand-by 1 LED per channel copper port activity 1 LED per channel copper port status
Alarm output	1 voltfree contact 1 A
Alarm function	Power supply fault Switch fault Data link status Redundancy ring fault
Ethernet cabling system	TF switches
Width	111 mm
Height	131 mm
Depth	111 mm
Product weight	0.6 kg

## Environment

Ambient air temperature for operation	0...60 °C
Relative humidity	10...95 % without condensation
IP degree of protection	IP20
Standards	CSA C22.2 No 142 CUL 60950 UL 1604 UL 508 CSA C22.2 No 213 Class I Division 2
Product certifications	C-Tick GL

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0616 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------

Dimensions

