



Zarges 40859– RS code: 2882523

Model No.	Inside Dimensions LXWXH mm	External dimensions LXWXH mm	Volume (approx.) L	Weight (KG)
40859	550x550x380	600x600x410	115	6.6



K 470 Universal container

The original since 1950. Perfect protection, even under extreme conditions.

- High-quality aluminum universal box
- Lid with stainless steel hinge strip, two lid straps and foamed seal all round.
- Cast-aluminum stacking corners.
- High level of stability due to 3 fully-welded aluminum profile frames
- Profile-section joints fully welded.
- Ergonomic & durable C. fasteners for at least 20,000 operating cycles.
- Snap fasteners: can be secured with a plug lock, lead seals, protection against bursting open or a padlock (max. shackle thickness 6 mm).
- Ergonomic heavy-duty sprung drop handles.
- Clearance dimensions approx. 30 mm less than inside dimensions.
- ZARGES Comfort handles for ergonomic handling and loads of up to 50 kg.
- 25 standard sizes, customized sizes available
- Beading all round and corner beads for additional dimensional stability.
- Extra strong 1.5 mm sheet with all K470 from 750 x 550 mm base dimension

Note

- Version with protection against water jets to class IP 65 available as an option
- UN approval for the transportation of hazardous goods possible at additional charge.
- Special inside inserts available on request.