


NO	DESCRIPTION	DATE
①	19-29-1/R19-029-01-002611000 → 40131101900001	05.24.19'
②	BERYLLIUM COPPER → BRASS	06.11.19'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-4 GHz
- 1.2 NOMINAL IMPEDANCE: 50 OHM
- 1.3 VOLTAGE RATING: 500 VOLTS MAX.
- 1.4 VSWR: 1.2 MAX.

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604 ②
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

- 4.1 INTERFACE IN ACCORDANCE WITH: MIL-STD-348A
- 4.2 RECOMMENDED COUPLING TORQUE: 3 TO 5 in-lbs

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -65° C TO +165° C

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
7	INSULATION	TEFLON	1	NONE
6	CENTER CONTACT	BRASS	1	GOLD
5	BODY	BRASS	1	NICKEL 100μ" MIN.
4	BODY	BRASS	1	NICKEL 100μ" MIN.
3	WASHER	STAINLESS STEEL	1	NONE
2	GASKET	SILICONE	1	RED
1	SHELL	BRASS	1	NICKEL 100μ" MIN.

APPROVED

by _____ DATE: _____

DESCRIPTION		STRAIGHT SMA PLUG-BNC JACK ADAPTER						
製圖	DRAWN	TOLERANCE	品名	40131101900001 ①	日期	DATE	版次	REV.
	Leona							
檢圖	CHECK	TOLERANCE	單位	UNIT	DWG.NO.	19-0130	佳楠精密電子股份有限公司	
	Amy							
認定	APPROVAL	TOLERANCE	比例	SCALE	CHIN NAN PRECISION ELECTRONICS CO.,LTD.			
	Jenny							