

# PHE F60FRTYRE



Size	F60
Nominal torque (Nm)	127
Nominal torque (lbft)	93.67
Max torque (Nm)	318
Max torque (lbft)	234.54
Max speed (r/min)	4000
Weight (kg)	0.5
Weight (lbs)	1.1