



Technical data

1R20X25X385

Inner rings

Needle roller bearing, inner ring

PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	20 mm
B - Bearing/Inner ring width	38,5 mm
F - Under roller diameter	25 mm
rs - Min fillet radius	0,3 mm
Lubrication hole on inner ring	Non/No
Precision class	P0
Mass	0,053 kg

ABUTMENT

da min - Min shoulder diameter IR	22 mm
ras max - Max shaft & housing fillet radius	0,3 mm