


Technical data sheet

Article number:**118-00081****T50MOS**

Product Group	Cable ties for thin-walled bundles
Product Family	OS-Series
Material	Polyamide 6.6 V0 (PA66V0)
Colour	White (WH)
Application Tool	MK3PNP2, EVOcut, MK7P, MK10-SB, MK20, EVO7SP, EVO7i, EVO7iSP
Bundle Ø max.	66.0 mm
Bundle Ø min.	1.6 mm
Flammability	UL 94 V0
Height (H)	1.3 mm
Length (L)	245 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +85 °C, (+105 °C, 500 h)
Package Content	100 pcs.
Package Content packed in	bag
Releasable Closure (Yes/No)	No
Specifications	EN 45545-2
Thickness (T)	1.3 mm
Toothing (Serration)	Outside Serrated
Variant	Outside Serrated
Weight/Unit	0.00078 kg
Width (W)	4.6 mm

LFH ✓ RoHS ✓**EN 45545-2**