




LOC	DIST	REVISIONS					
J		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	REVISED	25APR11	MM	NY



RECOMENDED PC BOARD HOLE PATTERN (TOL: ±0.05)
 PC BOARD THICKNESS: 1.6 ± 0.3
 (CONNECTOR MOUNT SIDE)




1318127-2
 9-1318127-2
 (KEYING Y)
 SCALE: 2-1

NOTES

- 1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, POLYESTER (94V-0), COLOR: 1318127-1/-2 : BLACK, 9-1318127-2 : NATURAL
- TAB CONTACT: COPPER ALLOY
- RETENTION LEG: BRASS
- 2. FINISH (CONTACT AREA): 0.38 μm MIN GOLD PLATING OVER Ni PLATING
- 3. FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL

Y	NATURAL	9-1318127-2
Y	BLACK	1318127-2
X	BLACK	1318127-1
KEY	COLOR	PART NO



1318127-1
 (KEYING X)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.IKEDA 07DEC98	TE Connectivity	
DIMENSIONS: mm		CHK N.MATSUBARA 07DEC98		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD I.HASEGAWA 07DEC98	NAME DOUBLE ROW HEADER ASS'Y 20P ("V" TYPE) <DYNAMIC D-2100D>	
0 PLC ± -		PRODUCT SPEC 108-5619	SIZE A3	
1 PLC ± 0.3		APPLICATION SPEC 114-5218	CAGE CODE 00779	DRAWING NO C-1318127
2 PLC ± 0.35		WEIGHT	RESTRICTED TO	
3 PLC ± 0.4		CUSTOMER DRAWING	SCALE 1:1	
4 PLC ± -			SHEET 1 OF 1	
ANGLES ± 3'		REV C		
FINISH SEE NOTES				