



| | | |
|-------------|---------|-----|
| APPROVED | DATE | REV |
| 5.95 TO 5.0 | 3-25-92 | 1 |

0.187 x 0.406
(2 PER BRACKET)



| | | | |
|----------|-------------|-------------|-------------|
| 60AYT6C | 11.580 MAX. | 13.615 MAX. | 12.892 MAX. |
| 45AYT6C | 11.580 MAX. | 13.615 MAX. | 12.892 MAX. |
| 60AYP6C | 7.160 MAX. | 9.195 MAX. | 8.472 MAX. |
| 45AYP6C | 7.160 MAX. | 9.195 MAX. | 8.472 MAX. |
| PART NO. | DIM. "A" | DIM. "B" | DIM. "C" |

MOUNTING BRACKET KIT
AA 405



45AYP6C & 60AYP6C / 45AYT6C & 60AYT6C
WITH BRACKETS

This document is proprietary to CORCOM INC. and is not to be reproduced nor used for manufacturing purposes except on CORCOM's order or prior written consent.

| | | | |
|---------|------------|-----------------------|------|
| SCALE | DATE | DRG. NO. | REV. |
| .6x | 11-6-89 | AYP-AYT.CUST.DRG-2.01 | |
| DRW. BY | ORIGINATOR | | |
| LJD | CFW | | |