

Specifications



Photo is representative



Eaton FAZ-C3/2-RT

Eaton FAZ branch protector, UL 1077 Industrial miniature circuit breaker - supplementary protector, Medium levels of inrush current are expected, 3 A, 15 kAIC, Two-pole, 277/480 V, 5-10X /n, 50-60 Hz, Ring-tongue terminals, C Curve

General specifications

PRODUCT NAME	Eaton FAZ branch protector
CATALOG NUMBER	FAZ-C3/2-RT
EAN	4015081020775
PRODUCT LENGTH/DEPTH	3.5 in
PRODUCT HEIGHT	2.8 in
PRODUCT WIDTH	1.38 in
PRODUCT WEIGHT	0.55 lb
WARRANTY	1 year
CERTIFICATIONS	UL 1077 CSA Std. C22.2 No.235 IEC 60947-2
CATALOG NOTES	Positioned for medium inrush startup currents to provide protection for small transformers and pilot devices.



Powering Business Worldwide

Physical Attributes

NUMBER OF POLES	Two-pole
TERMINALS	Ring-tongue
TYPE	UL 1077 Industrial miniature circuit breaker - supplementary protector

Miscellaneous

APPLICATION	Suitable for applications where medium levels of inrush current are expected
--------------------	--

Performance Ratings

AMPERAGE RATING	3 A
CIRCUIT PROTECTION	C curve
FREQUENCY RATING	50-60 Hz
INTERRUPT RATING	15 kAIC
TRIP TYPE	5-10X /n
VOLTAGE RATING	277/480V

Resources

CATALOGS	Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - FAZ-C3/2-RT

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.