


## Technical data

**KH2540**  
Ball sleeves



### VISUAL (S)



### PRODUCT DEFINITION

<b>Brand</b>	NTN
<b>Design type</b>	KH
<b>Ball bushings category</b>	Ball sleeves
<b>Standard</b>	ISO dimension
<b>Material outer cylinder or steel segments</b>	hardened steel sleeve
<b>Material Cage</b>	PA
<b>Initial greasing</b>	Non/No
<b>Re-lubricable</b>	Oui/Yes
<b>d - Internal diameter</b>	25 mm



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

### PRODUCT DEFINITION

<b>D - External diameter</b>	35 mm
<b>L - Length</b>	40 mm
<b>Number of ball rows</b>	6
<b>Mass</b>	0,066 kg

### PRODUCT PERFORMANCE

<b>Cmin</b>	1930000 mN
<b>Cmax</b>	1930000 mN
<b>C0min</b>	1560000 mN
<b>C0max</b>	1560000 mN
<b>Tmin - Min operating temperature</b>	253,15 °K
<b>Tmax - Max operating temperature</b>	353,15 °K

