

KSW3600EU

Housed within the 1.5mm high grade steel bodies these compact, rugged, reliable and built to last powerful ventilation fans can deliver up to 3600m³/hr at 343Pa. Available in either 110V or 240V and with optional 10m of flexible fire retardant ducting. Supplied with Euro Plug.

Diameter: 300mm
Supply: 110V/26A or 240V/13A
Airflow: 3600m³/hr
Static Pressure: 343Pa
Weight: 14kg
Dimensions: 44cm x 37cm

