

Datasheet

RS Pro On/Off Temperature Controller, 72 x 72mm, Digital Input, 100 → 240 V ac Supply

RS Stock No: 875-1292



Product Details

RS Pro on/off temperature controller of size 72 x 72 mm, comes with digital input and has a supply voltage of 100 - 240 V ac. Digital potentiometer control panel for V/F speed controller is designed for controlling the speed and direction of the motor as a control panel for V/F speed controllers in industry. They can be used in many applications with their easy use and operation with their ramp properties.

Features and Benefits

- 4 digits display
- Easily adjustable set value from front panel
- Configurable display scale between -1999 and 9999
- Adjustable decimal point
- Set value low and high limit boundaries
- Adjustable ramp up and ramp down time
- Forward, reverse direction outputs and error inputs for V/F speed controller
- Password protection for programming and adjustment sections

**Specifications:**

| | |
|-------------------------------|-----------------|
| Input Type | Digital |
| IP Rating | NEMA 4X |
| Maximum Operating Temperature | +50°C |
| Minimum Operating Temperature | 0°C |
| Mounting Type | 1/8 DIN Rail |
| Number of Inputs | 1 |
| Number of Outputs | 1 |
| Output Type | Current |
| Panel Depth | 95.5 mm |
| Size | 72 x 72 mm |
| Supply Voltage | 100 to 240 V ac |
| Termination Type | Screw |
| Panel Cut Out Size | 69 x 69 mm |