

Eaton 24AFIHA63

Catalog Number: 24AFIHA63

Eaton Bussmann series medium voltage BS air fuse, 63 A, 24 kV, 16 kA, 76.2 x 565 , With Striker

General specifications



| Product Name | Catalog Number |
|--|----------------|
| Eaton Bussmann series medium voltage BS air fuse | 24AFIHA63 |
| | EAN |
| | 5027590037747 |
| Product Length/Depth | Product Height |
| 565 mm | 76.2 mm |
| Product Width | Product Weight |
| 76.2 mm | 6100 g |
| Compliances | Certifications |
| BS 2692-1 | KEMA Certified |

Product specifications

Resources

Used with

A3354730 Fuse clip

Type

Fuse

Application

protection of primary side
transformers
used in fuse switch
combination units, fuse
bases and fuse switches

Amperage Rating

63 A

Fuse indicator

With Striker

Fuse size

76.2 x 565 mm

Breaking capacity

16 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

British Standard

Utilization category

Other

Voltage type

AC

With striker

Yes

Class

Class back-up

Fuse shape

Cylindrical

Pre arc (I²T)

3.2 x 103

Resistance

23.5 ohms

Fuse diameter

76 mm

Interrupt rating

16 kAIC

Construction size

76.2 x 565 mm

Mounting method

Clip-in

Voltage rating

24 kV

Fuse type

AFIH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia