

## **Product information**

12 49 02

## 1 pair of spare clamping jaws for 12 40 • With wire cutter for copper and aluminium wires, multiple stranded up 200



- For single, multiple and fine stranded conductors with plastic or rubber insulation
- Adapts automatically to the respective cable cross-section; prevents damage to the conductor
- Cutting depth can be adjusted for different insulation materials
- to 10 mm² and single stranded up to 6 mm²
- Smoothly operating mechanism
- Stripping blades and clamping jaws easily replaceable
- Low weight
- · Body: plastic, fibreglass-reinforced
- Blade: special tool steel, oil-hardened

| General         |               |
|-----------------|---------------|
| Article No.     | 12 49 02      |
| EAN             | 4003773026686 |
| Weight          | 2 g           |
| Dimensions      | 70 x 5 mm     |
| REACH compliant | no            |
| RohS compliant  | no            |

| Classification |            |  |
|----------------|------------|--|
| eCl@ss 5.1.4   | 21040302   |  |
| ETIM 5.0       | EC000163   |  |
| ETIM 6.0       | EC000163   |  |
| proficl@ss 6.0 | AAA002c003 |  |
| UNSPSC 13.1    | 27112100   |  |

technical change and errors excepted