



## KCC 22

E1621361

CABLE CUTTER 1-HANDED WITH SLITTING SHEAR, 0.2-35mm<sup>2</sup>, BOX

### Product Properties:

Grip design	1-component
With impact protection	No
Suitable for steel wire braiding	No
Replaceable cutting head	No
Cutting jaws exchangeable	No
With strip function	Yes
Insulated	Yes
Suitable for solid cores	Yes
Suitable for stranded conductors	Yes
Suitable for fine strand conductors	Yes
Construction/operation	Mechanic one hand
Isolation protection 1000 V	No
With spring	No

### Dimensions:

Max. cable cross section	35 mm <sup>2</sup>
MOQ	1 .
Unit	pcs
Suitable for max. cable diameter	10 mm
Total length	162 mm

### **Approvals:**

VDE tested	No
Isolation protection 1000 V	No

### **Compliance:**

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	In compliance
PFAS	No PFAS
REACH	No SVHC (250 Subs. 25 June 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)

### **Other information:**

ETIM-Class	EC000142 - Cable shears
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	1-hand
Search Description	CCTOOLS
Alternative SKU	KCC22
E-no	E1621361

### **Logistic information:**

Barcode	733117635414
Country of origin	JP
E-no	E1621361
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	KCC 22
Taric code	82032000
Unit	pcs

\*We reserve the right to make technical changes and disclaim any typographical errors.

