

Features

- High-quality LED light source
- High-energy density lithium battery
- High-strength ALuminum alloy
- Max. 1800LM
- High-Medium-Low-Strobe-SOS
- Type-C fast charge,
- 26650 3.7V 5000MAH Li-ion battery
- Power bank function:USB Max. 5V2A output
- IPX4

RS PRO Max. 1800lm 18W 5V/2A 6500K Torches

RS Stock No.: 0707147



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every

part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO SD-2500 Torch is made of high-quality LED light source, high-energy density lithium battery and high-strength aluminium alloy.

- *The surface of the lamp is specially treated.*
- *It has the characteristics of high brightness, long endurance, anti-falling, wear resistance and waterproof.*
- *The products can be used in daily family temporary lighting, emergency lighting, outdoor mountaineering, hiking, camping, work inspection, search, security lights, various occasions, a wide range of applications, convenient and flexible operation.*
- *Focusing lamp head can meet the needs of different scenes.*
- *Can be used as fishing light, EDC light or household patrol light.*
- *Using A7070 white laser LED, with a service life of 50,000 hours*
- *Can be used with strobe, SOS mode in emergency situations.*

General Specifications

Torch Style	Straight, Rotating Cap; With adjustable focusing
Lamp Type	LED
Luminosity	1800lm
Beam Type	Spot; Flood
Switching Modes	High-Medium-Low Double click - Strobe-SOS

Indicator Light	Blue-Working, Blue-charging
Light Colour	White;
Number of LEDs	1;
Colour	Silver
Case Material	Aluminium
Anti-Corrosive	Yes
Drop Resistance	1m
Hazardous Area	No; Yes
Wattage	18W
Operation Time	High:3H Low:11H
Colour Temperature	6500K

Modes Specifications

Parameters	High Mode	Medium Mode	Low Mode / Strobe	Flash ON/OFF / SOS
Light Output	1800lm	1200lm	500lm	1800lm
Run Time	4.4 hours	8 hours	5.5 hours	

Electrical Specifications

Rechargeable	Yes
Plug Type	USB - Type C
Batteries	26650 3.7V 5000MAH
Charging Time	6 hours
LED Charging Indicator	Blue-Charging
Battery Indicator	Yes
Switch Type	Switch
Input	5V 2A
Battery Protection	Intelligent overcharge/Discharge protection

Mechanical Specifications

Size	176.6*34*49MM
Head Diameter	49mm

Weight (with Batteries)	356g
Accessory	Type C USB cable, hanging wire

Protection Category

IP Rating	IPX4
-----------	------

Approvals

Compliance/Certifications	EMC/ROHS
Standards Met	EN IEC 55015:2019+A11:2020 EN IEC 61547:2023 RoHS Directive(EU)2015/863

WHAT INCLUDES / PACKAGING AND CONTENTS /
INSTALLATION & OPERATION / SAFETY WARNING