




Part Number : [1300130388](#)
Product Description : Mini-Change A-Size Bulkhead Feed-Through, 4 Poles, 7/8-16UN, Nickel Plated Brass, 0.049m (1.94") Length, 300V
Series Number : 130013
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : 1R4030



Documents & Resources

Drawings
[1300130388_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130013
Description	Mini-Change A-Size Bulkhead Feed-Through, 4 Poles, 7/8-16UN, Nickel Plated Brass, 0.049m (1.94") Length, 300V
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Mini-Change
Type	Bulkhead Feed-Through
UPC	78172553866

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V AC/DC

Physical

Coupling Type	Internal Thread
Gender	Female-Male
Keyway	Single
Length	0.049m
Material - Component	Nickel-plated Brass
Mounting Thread Size	7/8" - 16 UN-2A
Net Weight	91.172/g
Orientation	Straight
Panel Mount	Front

Poles	4
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	N/A
Wire Size (AWG)	N/A

This document was generated on Mar 27, 2025