

# PRODUCT DETAILS

## ARTICLE: [31529BFRHD](#)



### WHEEL LB 125X40/40 PB BOLT HOLE FORK X20 HOLE 14 + BRAKE

#### Wheel series LB

Wheels with black polyamide 6 centre, blue elastic non-marking rubber mould-on solid tyre available with ball bearings, standard or stainless steel roller bearings of plain bore.  
Plain bore wheel.


#### Castor series INOX20

Inox20 series, polished stainless steel forks, swivels with double ball races.  
Trailing foot brake - total stop.  
Single bolt hole fixing for bolt diam. 12-14 mm.



#### Technical data

Wheel diameter	D	125 mm
Tyre width	E	40,0 mm
Bore diameter	d	15 mm
Weight article		1,340 kg
Hub width	L	40 mm
Overall height	H	159 mm
Fixing bolt diameter	g	M12-14
Offset	F	49 mm
Fork width	U	50 mm
Load Capacity		200 kg



#### Related Articles

Spare part wheel: [30114B](#)  
Basic version: [31529BHD](#)

#### GENERAL INFORMATION / RECOMMENDATIONS AND WARNINGS

The cited text and the complete catalogue in their most up-dated versions are available in the OEM's website page [www.lagspa.it/downloads](http://www.lagspa.it/downloads). The dimensions, descriptions, specifications and illustrations herein are indicative and subject to variations without notice. The fact that products are illustrated herein does not necessarily imply they are available from stock nor does it place us under any obligation to supply them. Tests carried out refer to the original products with original accessories: the replacement of one of the components with others of different manufacture might prevent the same results from being achieved and will automatically invalidate any guarantee. Please contact our technical service concerning any special application.