


## FEATURES

- **DALI2, Push Dimming, PWM:** Offers versatile dimming options for enhanced lighting control
- **6.25 A Driver Current:** Provides sufficient current for high-power LED applications
- **100 – 277 V AC Input Voltage:** Compatible with a wide range of power supplies
- **IP66 Rating:** Ensures protection against dust and powerful water jets, suitable for harsh environments
- **Constant Voltage Operation:** Delivers stable voltage output for consistent LED performance

## RS PRO 150W LED Driver, 24V Constant Voltage

RS Stock No: 642-786



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

This RS PRO LED Driver is designed to provide reliable power to LED lighting systems. With a maximum output power of 150W and a constant voltage of 24V, it ensures stable and efficient operation for various lighting applications. Its robust design and IP66 rating make it suitable for both indoor and outdoor use, offering protection against dust and water ingress.

### General Specifications

Dimming Operation	DALI2, Push Dimming, PWM
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver

### Electrical Specifications

Driver Current	6.25 A
Input Voltage	100-277 V ac
Input Voltage Type	AC
Maximum Output Power	150 W
Output Voltage	24 V

### Protection Category

IP Rating	IP66
-----------	------

### Approvals

Standards/Approvals	CE, EN55015, EN61000-3-2, EN61000-3-3, EN61000-4-2,3,4,5,6,11, EN61347-1, EN61347-2-13, EN61547, EN62493
---------------------	--