


TAPD410BS - Break Stem Open

General Part Information		
Product Description		TAPD410BS
Article Number		20129.00
Rivet Type	i	Break Stem Open
Standard Bulk Pack Quantity		10000.00
Application / Features	i	



Geometry / Dimensions / Performance		
Head Style	i	Domed
Body Diameter Ø (mm)		3.20
Body Length (mm)		11.50
Min. Grip Range (mm)		6.40
Max. Grip Range (mm)		7.90
Min. Hole Diameter (mm)		3.30
Max. Hole Diameter (mm)		3.40
Min. Flange Diameter (mm)		6.05
Max. Flange Diameter (mm)		6.65
Flange Thickness (mm)		1.10
Mandrel Diameter (mm)		1.83
Nominal Shear Strength (N)		800.00
Nominal Tensile Strength (N)		1200.00

Material / Finish / Weight		
Body Material	i	AlMg3.5
Mandrel Material		Steel
Finish		Clean
Weight per thousand (kg)		1.11