

Signet DL50/K Induction Loop Driver Kit



Technical Specifications:

Microphone Inputs:

- Two inputs on 3.5mm jack socket, 3.5mV adjustable priority

Line Input:

- Two phono sockets, 200mV adjustable sensitivity

Tone:

- Adjustable tone control, +16dB -20dB ay 1kHz

Output Connector:

- 2-part terminal block to connect to supplied 33m loop cable

Auxiliary Connector:

- 2-part terminal block for closing contact from doorbell etc.

Headphone Output:

- 3.5mm jack connector

Indicators:

- Green power on, Red input signal, Green to Yellow to Red loop strength

Loop Current:

- >2 Amp Peak signal current into supplied SINGLE TURN loop

AC Power Supply:

- 230 Volt AC, 50-60 Hz.
- Power consumption 20 W. Max.
- 12Vac supply via 2.1 mm concentric power plug

Dimensions:

- 40 x 80 x 185mm

Weight:

- 550g (amplifier only)